Product leaflet

ProductModel No.Ordering No.Powered air purifying respiratorSR 500H06-0112

Product Description

The SR 500 is a battery-powered fan that, together with a filter and an approved head top, is included in the Sundström fan-assisted respiratory protective device systems. The SR 500 can be used as an alternative to filter respirators in all situations in which these are recommended. This applies particularly to work that is hard, warm or of long duration.

The human interface may consist of a hood, face shield, half mask or full face mask. The fan is equipped with a filter, and the filtered air is fed through a hose to the human interface. The pressure then generated prevents surrounding pollutants from penetrating into the mask.

The characteristics of the SR 500 are as follows:

The battery is of lithium-ion type • Two battery alternatives, i.e. STD (Standard 2.2 Ah) and HD (Heavy Duty 3.6 Ah) • The charging time for the Standard battery is around 1.5 hours and for the Heavy Duty battery, about 2 hours • Equipped with two filters/combined filters • Operating time of up to 13 hours • The same control is used for starting, stopping and selection of operating status • Display with symbols • Equipped with automatic air flow control with compensation for air pressure and temperature • Can be used together with hoods SR 520, SR 530, SR 561, SR 562, face shield SR 540, half mask SR 900, full face mask SR 200, welding shield SR 590, helmet with visor SR 580 or welding shield/helmet with visor SR 584/SR 580.

Electronics ingress protection is approved in IP class IP67 according to IEC / EN 60529.

The SR 500 is also available in an explosion-protected version designated the SR 500 EX for use in a potentially explosive atmosphere (ATEX Directive 94/9/EC). See the separate product leaflet.

Technical specification

| | SR 500 | EN 12941:1998 + A2:2008 | EN12942:1998 + A2:2008 |
|--|--|----------------------------|---------------------------|
| Air flow, min/max | 175/240 l/min | ≥ 120 l/min | - |
| STD-battery/HD-Battery | 14.8V, 2.2 Ah/3.6 Ah | - | - |
| Operating times at 175/240 l/min: | | | |
| P3, STD-battery | 8 h (7 h³)/5 h (4 h³) | ≥ 4 h | ≥ 4 h |
| P3, HD- battery | 13 h (12 h³)/8 h (7 h³) | ≥ 4 h | ≥ 4 h |
| Weight with STD-battery and P3 filter | ≈ 1 350 g | ≤ 3,500 g | ≤ 3,500 g |
| Service conditions | -10 °C to +55 °C, < 90 % RH, 600 to 120 $^{\circ}$ | 00 hPa - | - |
| Storage conditions | -20 °C to +40 °C, $<$ 90 % RH | - | - |
| Low flow warning level | < 175 l/min | ≤ 175 l/min | ≤ 175 l/min |
| Assigned Protection Factor¹: SR 520, SR 55 SR 540, SR 561/562, SR 580, SR 584, SR 59 | , | - | - |
| Assigned Protection Factor ¹ SR 200 | 40 (TM3) | - | - |
| Nominal Protection Factor ² SR 520, SR 530 SR 540, SR 561/562, SR 580, SR 584, SR 59 | • | - | - |
| Nominal Protection Factor ² SR 200 | 2000 (TM3) | | |
| Approvals | EN 12941:1998 + A2:2008 EN 12942:1998 + A2:2008 | - | - |

- 1) Specified in BS 4275 and applies generally to all approved fan-assisted respiratory protective devices, regardless of the test results.
- 2) According to EN 529:2005.
- 3) SR 900 + SR 951/SR 952.



Head Office

Tel: +46-(0)8-562 370 00 Fax: +46-(0)8-562 370 20

Visiting address: Stockholmsvägen 33 SE-181 33 Lidingö



Tel: +46-(0)8-562 370 00 Fax: +46-(0)8-562 370 60

Visiting address: Västergatan 4 SE-341 50 Lagan





